



| Model | X1 | X2 | H |
|-------------|-----------|----------|------|
| Walk-In 50 | 485-493 | max 1500 | 2000 |
| Walk-In 55 | 535-543 | max 1500 | 2000 |
| Walk-In 60 | 585-593 | max 1500 | 2000 |
| Walk-In 65 | 635-643 | max 1500 | 2000 |
| Walk-In 70 | 685-693 | max 1500 | 2000 |
| Walk-In 75 | 735-743 | max 1500 | 2000 |
| Walk-In 80 | 785-793 | max 1500 | 2000 |
| Walk-In 85 | 835-843 | max 1500 | 2000 |
| Walk-In 90 | 885-893 | max 1500 | 2000 |
| Walk-In 95 | 935-943 | max 1500 | 2000 |
| Walk-In 100 | 985-993 | max 1500 | 2000 |
| Walk-In 105 | 1035-1043 | max 1500 | 2000 |
| Walk-In 110 | 1085-1093 | max 1500 | 2000 |
| Walk-In 115 | 1135-1143 | max 1500 | 2000 |
| Walk-In 120 | 1185-1193 | max 1500 | 2000 |
| Walk-In 125 | 1235-1243 | max 1500 | 2000 |
| Walk-In 130 | 1285-1293 | max 1500 | 2000 |

| Model | X1 | X2 | H |
|-------------|-----------|----------|------|
| Walk-In 135 | 1335-1343 | max 1500 | 2000 |
| Walk-In 140 | 1385-1393 | max 1500 | 2000 |
| Walk-In 145 | 1435-1443 | max 1500 | 2000 |
| Walk-In 150 | 1485-1493 | max 1500 | 2000 |
| Walk-In 155 | 1535-1543 | max 1500 | 2000 |
| Walk-In 160 | 1585-1593 | max 1500 | 2000 |